

**V-9999-HW1 Mounting Kit to Mount
VA-715x or VA-720x Series Electric Actuators
to Honeywell® V5011A, F, and G, 1/2 through 3 inch
Single-Seated and V5013F Three-Way Valves**

The V-9999-HW1 Mounting Kit is designed to mount a VA-715x or VA-720x Series Electric Actuator to a Honeywell valve (up to a maximum stroke of 3/4 inch). Refer to the *VA-715x Electric Valve Actuator* or the *VA-720x Electric Valve Actuator* product/technical bulletins in the *Valve and Actuator Manual (FAN 977)* for complete actuator setup and calibration instructions.

Note: When mounting M100 Series Actuators to Honeywell valves, refer to the *Y20EBA Linkage Kit, M100 Motor Actuator to Honeywell Valves Technical Bulletin* in the *Valve and Actuator Manual (FAN 977)* for the appropriate linkage kit code number.

Kit Includes (See Figure 1)

- bonnet adaptor
- two 1/4-28 x 0.5 inch socket head cap screws
- one jam nut
- instruction sheet

Tools Required

- 3/16 inch Allen wrench




Figure 1: Exploded View of Mounting Kit Assembly to a Honeywell Valve




Figure 2: Mounting Kit Assembly Dimensions

Assembly Procedures

1. Slide bonnet adaptor over the valve's bonnet until it rests firmly on the mounting base.
2. Tighten set screws 1/8 to 1/4 turn clockwise beyond finger tight.
3. To correctly mount the actuator to the valve, refer to the appropriate actuator bulletin which corresponds to the selected actuator.
4. The adaptor kit and the actuator have now been correctly assembled to the valve.